

Screen Size

27"

Resolution

Full HD (1920 x 1080)

Aspect Ratio

16:9

Response Time

6 ms

Refresh Rate

60 Hz

Colours

16.7 million

Black

Contrast Ratio

100,000,000:1

Brightness

300 cd/m²

Backlight

LED

Panel Type

Vertical Alignment (VA)

Stand

Tiltable (-5° to 25°)

Ports & Connectors

DVI-in

HDMI®-in

VGA

Power

26.60 W (ENERGY STAR® rating)

32 W (EEL)

430 mW (standby)

240 mW (off)

Environmental Certification

TCO

Colours

16.7 million

Black

Dimensions (H x W x D)

14.5 inches x 24.2 inches x 9.5 inches (without stand)

17.7 inches x 24.2 inches x 9.5 inches (with stand)

Weight (Approximate)

9.3 lbs. (without stand)

11.5 lbs. (with stand)

Package Contents

V276HL Widescreen LCD Monitor

Power Cord

1 x VGA Cable

Warranty

[Standard Warranty](#)