



Pushing Performance



D SUB IP 67 Top entry plastic hood 25 p

Part number	09 67 025 0438
Description	D SUB IP 67 Top entry plastic hood 25 p

Identification

Category	Connector
Series of hoods/housings	D-Sub, IP67
Type of hood/housing	Shell
Description of hood/housing	With integrated cable gland
Locking type	Locking screw Thread 4-40 UNC

Version

Size	D-Sub 25
Version	Top entry
Details	Not to be used with crimp connectors.

Technical characteristics

Degree of protection acc. to IEC 60529	IP67
---	------

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Net weight	31.33 g