

■ **800 Watt Angle Grinder**
W 8-115 QUICK / W 8-125 QUICK

metabo[®]
work. don't play.



NEW

- High-powered angle grinder with extra high cooling capacity for fast work progress even under the toughest operating conditions
- Sturdy, durable Metabo marathon motor
- Metabo dust protection technology for ensuring the extremely long service of the unit: marathon motor with winding protection grid, fully enclosed switch, labyrinth seals on the ball bearing
- Ergonomic housing design with distinctive indents for comfortably holding the device during clearing and roughing, as well as slip-proof holding of the unit
- Diecast aluminium gear unit housing: robust and resistant to wear
- Metabo S-automatic torque limiting clutch: to limit any sudden reverse torque that can occur if tools jam or get caught.
- Safety switch prevents inadvertent switching on
- Metabo "Quick": quick tool change without using a key - quick, comfortable and safe
- Additional vibration damping Metabo VibraTech (MVT) handle for convenient continuous operation
- The tool-free adjustment and removal of the protective cover allows you to adjust the device for any application in seconds
- Highly durable switch-off carbon brush with dust protection housing

Grinding wheel Ø	115 mm
Torque	2,2 Nm
No load speed	10.000 /min
Rated input power	800 W
Output power	490 W
Rated load speed	7.000 /min
Spindle thread	M 14
Weight (without mains cable)	1,8 kg

Scope of delivery:

Protective cover, Inner support flange, "Quick" flange nut, Metabo VibraTech (MVT) handle

	Verpackung	Best.Nr.	EAN-Code
W 8-115 Quick	Karton	6.00264.00	4007430163332
W 8-125 Quick	Karton	6.00266.00	4007430163325