

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192020013](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** NylaKrimp™ Butt Splice for 18-22 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
UL E32244

**General**

Product Family Splices  
Series [19202](#)  
Crimp Quality Equipment Yes  
Mil-Spec N/A  
MolexKits Yes  
Overview [Splices](#)  
Product Name Butt, NylaKrimp™  
UPC 800753047396

**Physical**

Barrel Type Closed - Brazed  
Color - Resin Red  
Flammability 94V-2  
Insulation Nylon (PA)  
Material - Metal Copper  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Net Weight 1.047/g  
Packaging Type Bag  
Temperature Range - Operating -55°C to +105°C  
Wire Insulation Diameter 3.56mm max.  
Wire Size AWG 18, 20, 22  
Wire Size mm<sup>2</sup> 0.35-0.80

**Electrical**


Voltage - Maximum 600V

**Material Info**

Engineering Number AS-N-345

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
Sales Drawing 60002-11C



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[19202 Series](#)