

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0561348000**  
**Status:** **Active**  
**Overview:** MicroClasp™ Wire-to-Board System  
**Description:** 2.00mm Pitch Crimp Terminal 56134, Female, 22-26 AWG, Reel, Phosphor Bronze, for 51242/51353/51382 Housings

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 5055960001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification SPK-56134-001-001 (PDF)</a>
<a href="#">Application Specification 5055960001-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<u>56134</u>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<u>MicroClasp™ Wire-to-Board System</u>
Product Name	MicroClasp™
UPC	800756190532


**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	36.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.25-1.70mm
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5055960001-000, 5055960001-001
Packaging Specification	SPK-56134-001-001
Sales Drawing	SD-56134-002



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

56134 Series

**Use With**

51242 Dual Row Crimp Housing, 51353  
Dual Row Crimp Housing, 51382 Single  
Row Crimp Housing