


GFBF20ILA -- Circuit Guard LED Blank Face GFCI

20A 125V, 2P 3W, Flush Thermoplastic Face, Back & Side Wired, Matching Wall Plate Included, Ivory



Faceless GFCI

Receptacle Version	Faceless
Receptacle Grade	Commercial
Faceless Type	LED Series
Amperage	20A
Color	 Ivory
Voltage	125V AC
Packaging	Single
Trip Level	4-6 mA
Trip Time	0.025 seconds
Frequency	60Hz
Voltage Range	120V AC +10% -15%
Amperage Range	20 Amps Feed Thru
Max Humidity	0.95
Max Interrupting Capacity	2,000 Amps
Operating Temp	Deg F -30 to 150 (Deg C -30 to 66)

Codes and Standards	Meets UL 943 Class A GFCIs and UL 498 for Receptacles. Complies to NEC, CEC & OSHA. UL File E-41978, CSA File LR-24886
Terminal Accommodations	#14 -10 AWG stranded or solid copper conductors only.
Note:	GFCI Receptacles should not be used in critical care patient areas or for electrical life support equipment.
UPC Number	88377837919
Weight in LBs	0.3