

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0349674001](#)  
**Status:** **Active**  
**Overview:** [Mini50™ Connection Systems](#)  
**Description:** Mini50™ Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option A, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-31301-898 \(PDF\)](#) [Product Literature \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">34967</a>
Application	Power, Sealed, Wire-to-Board
Overview	<a href="#">Mini50™ Connection Systems</a>
Polarization	A
Product Literature Order No	987651-6273
Product Name	Mini50™ Sealed
UPC	887191620381

**Physical**

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	2.765/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-31301-898
Sales Drawing	349674000-000



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[34967 Series](#)

**Mates With**

Contact Molex for mating information.

**Use With**

CTX50 Sealed Receptacle Terminal  
[34905-2443](#) , [34905-2444](#)