

166-90178

Article Number: 166-90178



Description: HelaGuard PACC Conduit Clip, 0.38" Dia, PA66, Black, 10/pkg

Base Data	Local Order Number	166-90178
	Type	PACC0380
	Color	Black (BK)
	Features and benefits	• Assists with installation by easily cutting through HelaGuard non-mettalic conduit and tubing.
	Product Description	Conduit Clips clamp onto corrugated conduits and tubing to secure. Nylon material resists corrosion and chemicals. Can also be used on C-shaped DIN rails.
	Short Description	HelaGuard PACC Conduit Clip, 0.38" Dia, PA66, Black, 10/pkg
	Product Dimensions	Length L (Imperial)
Length L (Metric)		26mm
Fits Conduit Size (Imperial)		3/8 "
Fits Conduit Size (Metric)		16mm
Width W (Imperial)		0.47"
Width W (Metric)		12mm
Height H (Imperial)		1.18"
Height H (Metric)		30mm
Mounting Hole Diameter D (Imperial)		0.20"
Mounting Hole Diameter D (Metric)		5.0 mm
Nominal Diameter (Imperial)		3/8"
Nominal Diameter (Metric)		16mm
Material and Specifications		Material
	Material Shortcut	PA66
	Flammability	UL 94 V2

166-90178



Material and Specifications	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987