

Product data sheet

Characteristics

LV426801

undervoltage release (spring) MN - 24 V AC 50/60Hz - 24 V DC

Product availability : Stock - Normally stocked in distribution facility



Main

Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	PowerPact PowerPact B Compact Compact NSXm
Voltage release type	Undervoltage release
Control circuit voltage	24 V AC 24 V DC

Complementary

Threshold tripping voltage	0.35...0.7 x Un - during opening time 0.85 x Un - during closing time
Mounting mode	Clip-on
Response time	< 50 ms
Auxiliary connection terminal	Spring
Wire stripping length	0.31 in (8 mm)

Ordering and shipping details

Category	01136 - PP-B FRAME ACCESSORIES
Discount Schedule	DE2
GTIN	003606485412788
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14000000000000001
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold