



Main

Range compatibility	PowerPact B
Product or component type	Cable connector
Device short name	Connectors
Accessory / separate part type	Connection accessories
Poles description	3P

Complementary

Quantity per set	Set of 1
Location of connection	Downstream Upstream
[In] rated current	15...125 A for copper 15...100 A for aluminium
Conductor material	Steel
Connections - terminals	1 screw terminal 2.5...95 mm ² (AWG 14...AWG 3/0) (solid) Screw terminal 2.5...95 mm ² (AWG 14...AWG 3/0) (stranded) Screw terminal 2.5...70 mm ² (AWG 6...AWG 2/0) (fine stranded)
Current of common	10 A for 0.5...6 mm ² (AWG 20...AWG 10 , (stranded or fine stranded) 10 A for 1.5...6 mm ² (AWG 20...AWG 10 , (rigid)

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------