

# TY400-50X-100



Products Low Voltage Products and Systems Installation Products Wire Management and Connectivity Cable Ties

## General Information

<b>Extended Product Type:</b>	TY400-50X-100
<b>Product ID:</b>	7TAG054360R0337
<b>EAN:</b>	5414363075363
<b>Catalog Description:</b>	CBL TIE 50LB 14IN UV BLACK NYL
<b>Long Description:</b>	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA6227 5 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 365.76mm (14.4 Inches), Width of 4.673mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), Military Specified (MIL-SPEC MS-3367-2), 100 Pack

## Additional Information

<b>Brand / Label:</b>	TY-FAST
<b>Country of Origin:</b>	United States (US)
<b>Customs Tariff Number:</b>	3926909996
<b>Data Sheet, Technical Information:</b>	TY400-50X-100
<b>E-nummer:</b>	1519852
<b>EAN:</b>	5414363075363
<b>ETIM 6:</b>	EC000046 - Cable tie
<b>Instructions and Manuals:</b>	TY400-50X-100
<b>Invoice Description:</b>	CBL TIE 50LB 14IN UV BLACK NYL
<b>Minimum Order Quantity:</b>	100 piece
<b>Package Level 1 EAN:</b>	00075114952392
<b>Package Level 1 Height:</b>	43.18 mm
<b>Package Level 1 Length:</b>	457.2 mm
<b>Package Level 1 Units:</b>	100 piece
<b>Package Level 1 Width:</b>	152.4 mm
<b>Package Level 2 EAN:</b>	50075114952397
<b>Package Level 2 Height:</b>	142.24 mm
<b>Package Level 2 Length:</b>	391.16 mm
<b>Package Level 2 Units:</b>	500 piece
<b>Package Level 2 Width:</b>	147.32 mm
<b>Product Main Type:</b>	CABLE TIES AND ACCESSORIES
<b>Product Name:</b>	CATAMOUNT FASTENING PRODUCTS
<b>Product Net Weight:</b>	2.554 g
<b>Selling Unit of Measure:</b>	each
<b>UNSPSC:</b>	39121703
<b>UPC:</b>	075114952392

