

TY225-50-100



Products Low Voltage Products and Systems Installation Products Wire Management and Connectivity Cable Ties

General Information

Extended Product Type:	TY225-50-100
Product ID:	7TCG054360R0231
EAN:	5414363061342
Catalog Description:	CBL TIE 50LB 9IN NATURAL NYLON
Long Description:	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 215mm (8.46 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1.3mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), 100 Pack

Additional Information

Brand / Label:	TY-FAST
Country of Origin:	Hungary (HU)
Customs Tariff Number:	3926909996
Data Sheet, Technical Information:	TY225-50-100
E-nummer:	1519744
EAN:	5414363061342
ETIM 6:	EC000046 - Cable tie
Instructions and Manuals:	TY225-50-100
Invoice Description:	CBL TIE 50LB 9IN NATURAL NYLON
Minimum Order Quantity:	100 piece
Order Multiple:	100 piece
Package Level 1 EAN:	00786210698014
Package Level 1 Height:	127 mm
Package Level 1 Length:	381 mm
Package Level 1 Units:	100 piece
Package Level 1 Width:	25.4 mm
Package Level 2 EAN:	50786210698019
Package Level 2 Height:	355.6 mm
Package Level 2 Length:	501.65 mm
Package Level 2 Units:	5000 piece
Package Level 2 Width:	258.318 mm
Product Main Type:	CABLE TIES AND ACCESSORIES
Product Name:	CATAMOUNT FASTENING PRODUCTS
Product Net Weight:	0.853 g
Selling Unit of Measure:	each
UNSPSC:	39121703
UPC:	786210698014

