

Weller Micro Digital Rework Soldering Station, 120 V

◀◀ previous print close next ▶▶

Product Details

Catalog No.	WD1000M
UPC Code	037103215185
Wattage	40 W
Soldering Pencil(s)	WMRP
Temperature Range	150° F to 850° F
Voltage Input/Output	120 V/24 V
Supplied Tip(s)	RT3
Iron Stand	WMRH
Temperature Accuracy	+/- 17° F (9° C)
Packaging	Industrial Box/Carton
Literature	550517.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- **Designed for fine pitch, high density SMT soldering and rework**
- **3 "radio buttons" allows pre-set of frequently used temp settings**
- **Setback, lockout, temp. window, F/C switching, standby, auto-off time**
- **Large high contrast LCD display displays more information at a glance**
- **The heating element is contained in the tip for fast heat-up**
- **Pencil is made of aluminum with chrome plating and weighs just 75g**
- **The pencil powers down when placed in the holder to extend tip life**
- **The "tip to grip" distance is 45mm, placing you close to the work**
- **A swivel head on the stand allows for adjustment of the pencil tilt angle**
- **ESD safe to protect sensitive components**