

Wrap Bit, 26 AGW, Modified Wrap

◀◀ previous print close next ▶▶

Product Details

Catalog No.	502118
UPC Code	037103952011
Wire Type	Alloy, OFHC
Wire Size	26 AWG
Min/Max Terminal Diagonal	0.053/0.069 in.
Terminal Hole Depth	1.00 in.
Max. Insulation Diameter	0.041 in.
Min. no. of insulated turns	0.900
Effective Radius	0.111 in.
Packaging	Industrial Box/Carton
Tech. Spec.	<u>WW Tech Sheets.pdf</u>
Low Res. Image	<u>60152015-02_100.jpg</u>
High Res. Image	<u>60152015-02_300.jpg</u>
Stock Item	Made to Order-Call for Lead Time

Package Details (Dimensions)

Email this Page

Product Features:

- **Wire wrapping bits made from top quality materials**
- **Precision machined to exact tolerances**