

WetEx®



Models may vary from the image shown

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

Flexible protective film for keyboards.

If it happens more roughly. WetEx® protects keyboards from liquid spills, dust and dirt.

Key benefits

- Resistant to dish liquid
- Resistant to isopropyl alcohol
- Under normal conditions WetEx® provides > 10 Mio. operating cycles.
- Disposal does not cause polybrominated dibenzodioxin or dibenzofuran.
- Conditionally resistant to petrol
- Resistant to distilled water
- Resistant to Diesel
- WetEx® is free of halogens and latex.
- Conditionally resistant to 40% sulfuric acid (battery acid)
- WetEx® does not contain polybrominated diphenyl ethers.
- Conditionally resistant to oil

Technical Data:

- Elongation: 450%
- Tearing strength: 9000 PS
- Thickness: 0.25 mm
- Usage temperature: -40 °C to +71 °C
- Tensile strength: 400 lbs/inch
- Modulus of elasticity: 1200 PSI
- Spec. weight: 1.13 g/cm³
- Hardness: 84 IRHD
- Abrasion resistance: 6

Packaging Unit:

- Number of products in the master package: 10
- Keyboard layout features: Product dependant, see table "Models"
- Keyboard family: Product dependant, see table "Models"

Models:

	Product name	Order number	Keyboard family	Keyboard layout features ¹
1	WetEx®	6155044	• G84-4100	• no Windows keys • no context menu key
2	WetEx®	6155079	• G81-3000 • G80-3000	• 2 Windows keys (left/right) • 1 context menu key • "International" enter key
3	WetEx®	6155080	• G81-3000 • G80-3000	• 2 Windows keys (left/right) • 1 context menu key • "European" enter key
4	WetEx®	6155112	• G81-1800 • G80-1800	• 2 Windows keys (left/right) • 1 context menu key • "International" enter key
5	WetEx®	6155113	• G81-1800 • G80-1800	• 2 Windows keys (left/right) • 1 context menu key • "European" enter key
6	WetEx®	6155118	• G84-4100	• 2 Windows keys (left/right) • 1 context menu key
7	WetEx®	6155138	• G83-6104/G83-6105 • G83-6188	Variant 1: • 2 Windows keys (left/right) • 1 context menu key • "International" enter key Variant 2: • 1 context menu key • 2 "Linux" keys (left/right) • "International" enter key
8	WetEx®	6155139	• G83-6104/G83-6105 • G83-6188 • G83-6260 • G83-6236 • G83-6919LUNBY • G83-6919 • G83-6919LUNOY • G83-6919LUNVY • G83-6919LUNZY • G83-6919LUNHY • G83-6919LUNAY	Variant 1: • 2 Windows keys (left/right) • 1 context menu key • "European" enter key Variant 2: • 1 context menu key • 2 "Linux" keys (left/right) • "European" enter key
9	WetEx®	6155140	• G84-4400 • G84-4420	• "Narrow" shift key left
10	WetEx®	6155141	• G80-11900	• 2 Windows keys (left/right) • 1 context menu key • "European" enter key
11	WetEx®	6155142	• G80-11900	• 2 Windows keys (left/right) • 1 context menu key • "International" enter key
12	WetEx®	6155147	• G84-4400 • G84-4420	• "Wide" shift key left

	Product name	Order number	Keyboard family	Keyboard layout features ¹
13	WetEx®	6155173	• G84-4700	-
14	WetEx®	6155177	• G83-6744	<ul style="list-style-type: none"> • 2 Windows keys (left/right) • 1 context menu key • "International" enter key
15	WetEx®	6155178	• G83-6744	<ul style="list-style-type: none"> • 2 Windows keys (left/right) • 1 context menu key • "European" enter key
16	WetEx®	6155199	• G84-5200	<ul style="list-style-type: none"> • 1 Windows key (left) • 1 context menu key • "European" enter key
17	WetEx®	6155200	• G84-5200	<ul style="list-style-type: none"> • 1 Windows key (left) • 1 context menu key • "International" enter key
18	WetEx®	6155201	• G84-5400	<ul style="list-style-type: none"> • 1 Windows key (left) • 1 context menu key • "European" enter key
19	WetEx®	6155202	• G84-5400	<ul style="list-style-type: none"> • 1 Windows key (left) • 1 context menu key • "International" enter key
20	WetEx®	6155203	• G84-5500	<ul style="list-style-type: none"> • 1 Windows key (left) • 1 context menu key • "European" enter key
21	WetEx®	6155204	• G84-5500	<ul style="list-style-type: none"> • 1 Windows key (left) • 1 context menu key • "International" enter key
22	WetEx®	6155205	• G83-6644	<ul style="list-style-type: none"> • 2 Windows keys (left/right) • 1 context menu key • "European" enter key • "Narrow" shift key left
23	WetEx®	6155211	• G87-1504	<ul style="list-style-type: none"> • 2 Windows keys (left/right) • 1 context menu key • "European" enter key
24	WetEx®	6155216	<ul style="list-style-type: none"> • G85-23000 • G85-23100/G85-23110 • G85-23100 T2 • G85-23200 	<ul style="list-style-type: none"> • 2 Windows keys (left/right) • 1 context menu key • "European" enter key
25	WetEx®	6155217	<ul style="list-style-type: none"> • JK-0800 • JD-0700 • JK-1700 • JD-0800 	<ul style="list-style-type: none"> • 2 Windows keys (left/right) • 1 context menu key • "European" enter key
26	WetEx®	6155218	<ul style="list-style-type: none"> • JK-0700 • JK-0720 	-

1 Keyboard layout features:

- 2 Windows keys (left/right)



- 1 Windows key (left)



- 1 context menu key



- 2 "Linux" keys (left/right)



- "European" enter key




- "International" enter key



- no Windows keys



- "Wide" shift key left



- "Narrow" shift key left



- no context menu key

