

## Weller Marksman® Stained Glass Iron (80 Watt)



◀◀ previous print close next ▶▶

### Product Details

<b>Catalog No.</b>	<b>SPG80L</b>
<b>UPC Code</b>	<b>037103169136</b>
<b>Type</b>	<b>Stained Glass</b>
<b>Wattage</b>	<b>80 W</b>
<b>Temperature Range</b>	<b>900° F</b>
<b>Cord Length</b>	<b>6 ft.</b>
<b>Components Supplied</b>	<b>MTG20</b>
<b>Packaging</b>	<b>Peg Hook/Retail Packaging</b>
<b>Tech. Spec.</b>	<b><u><a href="#">Solder Safety Warnings.pdf</a></u></b>
<b>Lineart</b>	<b><u><a href="#">SPG80L.pdf</a></u></b>
<b>Low Res. Image</b>	<b><u><a href="#">SPG80L_100.jpg</a></u></b>
<b>High Res. Image</b>	<b><u><a href="#">SPG80L_300.jpg</a></u></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

### Package Details (Dimensions)

[Email this Page](#)

#### Product Features:

- SP80L iron, MTG20 and MTG21 tips, and soldering iron rest
- New indicator light allows you to instantly see that the iron is on
- Can tackle intricate seams repair old ones, ideal for stained glass work
- Simple and safe to use
- Helpful hints and instructions inside clamshell
- Marksman® soldering tips available
- **IMPORTANT: Use only Weller® tips**
- UL listed - cUL version available