

Weller Marksman® Iron (175 Watt)



◀◀ previous print close next ▶▶

Product Details

Catalog No.	SP175
UPC Code	037103474674
Type	Non-temperature Controlled
Wattage	175 W
Temperature Range	900° F
Cord Length	6 ft.
Components Supplied	MTG40
Packaging	Peg Hook/Retail Packaging
Tech. Spec.	<u>Solder Safety Warnings.pdf</u>
Low Res. Image	<u>SP175_100.jpg</u>
High Res. Image	<u>SP175_300.jpg</u>
Stock Item	Normal Stock Item

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- Fine quality heavy duty consumer iron, 12 1/2"/318mm long
- Extra heavy duty for demanding jobs like sheet metal work
- Soldering iron rest included
- MTG40 5/8"/16mm diameter replaceable iron-plated copper tip
- Develops 900°F/482°C temperature
- Stainless steel barrel and heat and impact resistant handle
- **IMPORTANT: Use only Weller® tips**
- UL listed - cUL version available