

Xcelite 5" General-purpose Shearcutter with Static-dissapative Black Grips



◀◀ previous print close next ▶▶

Product Details

Catalog No.	175D
UPC Code	037103030009
Description	Diagonal
Jaw Type	Flush
Jaw Length	3/4 in.
Head Width	11/32 in.
Head Thickness	1/2 in.
Tip Dimensions	5/64 in.
Packaging	Peg Hook/Retail Packaging
Tech. Spec.	170M_Specifications.pdf
Low Res. Image	170D_100.jpg
High Res. Image	170D_300.jpg
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- **Low profile, general-purpose cutter**
- **Superior blade by-pass shear cutting action**
- **Better cuts with half the effort**
- **Greatly reduced mechanical shock delivered to the work**
- **Features static-dissapative black grips**
- **Especially hardened and plated**
- **Features safety clips**
- **Flush cuts soft wire up to 20 AWG (0.8mm)**