

KEMET Part Number: PMR209MB5470M047R30
(P409QM473M250AH470)

Film, Metallized Paper, Resistor/Capacitor, PMR209/P409, 0.047 uF, 20%, 630 V, 85C, Lead Spacing = 15.2mm



General Information	
Dielectric:	Metallized Paper
Style:	Radial
Series:	PMR209/P409
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Construction:	Molded
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart). Resistor= 47 Ohms

Dimensions	
L	18.5mm MAX
H	13mm MAX
T	7.3mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	0.047 uF
Capacitance Tolerance:	20%
Voltage DC:	630 VDC
Voltage AC:	250 VAC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Insulation Resistance:	3 GOhms
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	400