

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015979121](#)
Status: **Active**
Overview: Mini-Fit® TPA2 Plugs and Receptacles
Description: Mini-Fit® TPA Key for 12 Circuit

Documents:

[3D Model](#) [Packaging Specification PK-30072-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5556-003 \(PDF\)](#)

General

Product Family Crimp Housings
 Series [30072](#)
 Application Power, Wire-to-Board, Wire-to-Wire
 Overview [Mini-Fit® TPA2 Plugs and Receptacles](#)
 Product Name Mini-Fit® TPA
 UPC 800754203104

Physical

Circuits (maximum) 12
 Color - Resin Natural
 Gender Receptacle
 Glow-Wire Compliant No
 Material - Resin Nylon
 Net Weight 0.256/g
 Number of Rows 2
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 4.20mm
 Stackable No
 Temperature Range - Operating -40°C to +105°C

Electrical


Current - Maximum per Contact 13.0A

Material Info

Engineering Number 30072-12

Reference - Drawing Numbers

Packaging Specification PK-30072-001-001
 Product Specification PS-5556-003
 Sales Drawing SD-30072-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[30072](#) Series

Mates With

[30068](#) , [30069](#) , [30069](#) , [30070](#) , [30070](#) ,
[44473](#)

Use With

[30067](#) 4.20mm Pitch Mini-Fit® Crimp
 Housing