

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0887283400**
Status: **Active**
Overview: Consumer USB Products
Description: Universal Serial Bus (USB) Shielded I/O Cable Assembly: A-to-Pigtail Full-Rated, 2.08m Length

Documents:

[3D Model](#) [Packaging Specification PK-88728-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88740
Assembly Configuration	Single Ended Connector
Comments	Full-rated
Connector to Connector	USB Type A-to-Pigtail
Overview	Consumer USB Products
Product Name	USB
UPC	800754341738

Physical

Cable Length	2.08m
Circuits (Loaded)	4
Gender	Male
Lock to Mating Part	Yes
Net Weight	69.600/g
Packaging Type	Bag
Pitch - Mating Interface	2.00mm, 2.50mm
Single Ended	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round


Electrical

Current - Maximum per Contact	1.0A
Shielded	Yes

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-88728-002
Sales Drawing	SD-88738-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant*

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from product compliance status evaluation.
CUST_NOTE2	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[88740 Series](#)

Mates With

Universal Serial Bus (USB) Type A Receptacle 67329 , 67230 , 89485