

Weller

Weller Soldering Ironw/LED's (40 Watt)

◀◀ previous print close next ▶▶

Product Details

Catalog No.	SP40NUS
UPC Code	037103266927
Type	40W
Wattage	900°F / 482°C
Temperature Range	6 ft.
Cord Length	MT10 0.250" (6.35mm) Chisel
Components Supplied	Peg Hook Retail/Packaging
Tech. Spec.	<u>Solder Safety Warnings.pdf</u>
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- **Three LED lights for limited application shadowing**
- **Round Co-molded soft grip handle design for easy tip positioning**
- **Triangular handle area for maximum tip control**
- **Stainless steel barrel and heater**
- **UL listed - cUL version available**
- **Excellent quality consumer iron 8 1/4" (210mm) long**
- **Medium duty iron, (40watts) for joining 12 AWG wire or smaller**
- **Use on electrical/electronic components, audio equip., RC hobbies, etc.**
- **IMPORTANT: Use only Weller® tips**