

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0457190003**
Status: **Active**
Overview: Edge Card Connectors
Description: 12.90mm Pitch EXTreme PowerEdge™, Through Hole Solder for 3.18mm Thick PC Board, Mates to a 1.57mm Thick Card Edge or Bus Bar Tab

Documents:

[3D Model](#) [Packaging Specification PK-45714-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
TUV R72090228

General

Product Family Edge Card Connectors
Series 45719
Circuit Size Range 1-64 Circuits
Component Type Edgcard to PCB
Data Rate Unrated
Edge Card Thickness 1.57mm
High Power Bay (30.0A or more) Yes
Orientation Vertical
Overview [Edge Card Connectors](#)
Product Name Bus Bar Socket, EXTreme PowerEdge™
Standard Based General
UPC 822348678556

Physical


(p)ower-(s)ignal Configuration 8p - 0s
Circuits (Loaded) 8
Circuits (maximum) 8
Color - Resin Black
Durability (mating cycles max) 200
Entry Angle Vertical (Top Entry)
Flammability 94V-0
Keying to Mating Part N/A
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 9.864/g
PC Tail Length 4.50mm
PCB Thickness - Recommended 3.20mm
Packaging Type Tray
Pitch - Mating Interface 12.90mm
Plating min - Mating 0.762µm
Plating min - Termination 3.810µm
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 40.0A
Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-freeProcess Capability WAVE



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

45719 Series

Mates With

1.58mm Double Sided Card Edge or Bus Bar Tab

Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	250

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-45714-001
Sales Drawing	SD-45719-001

This document was generated on 05/03/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION