

0 603 9A2 172 – EasyDrill 1200

| | |
|--------------------------------------|---------------|
| Material number | 0 603 9A2 172 |
| EAN | 4053423201352 |
| Baretool number | 3603JA2102 |
| AL 1110 CV charger 2 609 120 553 | ✓ |
| Carrying case 2.1 | ✓ |
| Double screwdriver bit | ✓ |
| PBA 12 V 1.5 Ah O-A 1 607 A35 07R | ✓ |



Technical data

Description

| | |
|--------------------------|-----------------------|
| Product name (formatted) | EasyDrill 1200 |
|--------------------------|-----------------------|



Technical data

| | |
|---|---------------------|
| Battery voltage | 12,0 V |
| Battery capacity | 1.5 Ah |
| No-load speed (1st gear / 2nd gear) | 0 – 450 / 1.650 rpm |
| No-load speed | 0 – 1.650 rpm |
| Max. torque | 20,0 Nm |
| Max. torque for soft/hard screw. applications | 11 / 20 Nm |
| Torque settings | 15 + 1 |
| Drill chuck | Keyless chuck |
| Machine weight with battery | 1,00 kg |

Screw diameter

| | |
|----------------------|------|
| Screw diameter up to | 6 mm |
|----------------------|------|

Drilling diameter

| | |
|----------------------------|-------|
| Drilling diameter in steel | 6 mm |
| Drilling diameter in wood | 20 mm |

Functions

| | |
|--|---|
| 12 Volt | ✓ |
| Lithium-ion technology | ✓ |
| Bosch Electronic Cell Protection (ECP) | ✓ |
| 2-speed gearbox | ✓ |
| Application: screwdriving / drilling | ✓ |
| Softgrip | ✓ |
| Integrated work light | ✓ |
| Bosch Electronic | ✓ |
| Right-hand/left-hand rotation | ✓ |
| Forward/reverse indicator | ✓ |

Noise/vibration information

| | |
|----------------------|--|
| Sound pressure level | 66 dB(A) |
| Sound power level | 77 dB(A) |
| Uncertainty K | 3 dB |
| Noise level | The A-rated noise level of the power tool is typically as follows: Sound pressure level 66 dB(A); Sound power level 77 dB(A). Uncertainty K= 3 dB. |



Sales information

Positioning

- Small, lightweight, powerful – Cordless power with good value for money

User benefit

- Syneon Chip: Intelligent control of the energy for optimum power and maximum
- endurance No memory effect, no self-discharge: Always ready to use thanks to lithium-
- ion technology Compact design thanks to lithium-ion technology

Other features

- Bosch Electronic speed control: “accelerate” from 0 – max. using the trigger switch High-
- performance planetary gearbox: superior lifetime, best power transfer, high running smoothness
- PowerLight – thanks to the built-in LED, your workpiece is always well lit and clearly visible
- Torque preselection with 15 torque settings plus a drill setting – optimum power for every application