



### Main

Range of product	Preventa XY2
Product or component type	Simple rope pull switch
Device short name	XY2CD
Housing colour	Blue
Overtoltage category	Class I conforming to EN/IEC 61140 Class I conforming to NF C 20-030

### Complementary

Trigger cable maximum length	6 m
Body material	Zamak
Head material	Plastic
[Us] rated supply voltage	240 V
Contacts type and composition	1 NC + 1 NO
Contacts operation	Snap action
Operating force	237 daN
Pulling force	36 daN
Cable entry number	3 3 entries tapped for Pg 13.5 cable gland Pg 13.5
Mechanical durability	1500000 cycles
[Ie] rated operational current	3 A at 240 V AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	300 V (degree of pollution: conforming to UL 508) 300 V (degree of pollution: conforming to CSA C22.2 No 14) 400 V (degree of pollution: 3) conforming to EN/IEC 60947-1

## Environment

Product certifications	CCC CE
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
IP degree of protection	IP66 conforming to IEC 60529

## Ordering and shipping details

Category	22441 - LIMIT SWITCHES,CABLE PULL
GTIN	003389110662016
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7000000000000007
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------