



Main

Product or component type	Single Unit Manual Switch
Range of product	K
Line Rated Current	30 A
Product certifications	UL listed CE CSA
Cable entry	0.75 NPT (top and bottom)
NEMA degree of protection	NEMA 4 die cast zinc alloy standard size
Motor power hp	1 hp 90 V DC 10 hp 460 V AC 10 hp 575 V AC 2 hp 115 V AC 2 hp 115 V DC 1.5 hp 230 V DC 7.5 hp 230 V AC
System Voltage	600 V AC 230 V DC
Poles description	3P
Control type	Toggle
Phase	3 phases
Local signalling	Red indicator 440...600 V
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
GTIN	00785901376415
Nbr. of units in pkg.	1
Package weight(Lbs)	3.0100000000000002

May 19, 2017

Returnability	N
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
