



### Main

Device short name	K
Mounting diameter	1.18 in (30 mm)

### Complementary

Line Rated Current	5 A
Contact operation	Standard fingersafe
Contacts material	Gold flashed contacts
Contacts type and composition	1 NO
Electrical connection	Screw clamp terminal
Permissible voltage	<= 300 V

### Environment

Product certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE
------------------------	---

### Ordering and shipping details

Category	21434 - 9001 KA CONTACT BLOCKS
GTIN	00785901028895
Nbr. of units in pkg.	1
Package weight(Lbs)	5.0000000000000003E-2
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity
------------------------	---

---

REACH

Reference not containing SVHC above the threshold  
Reference not containing SVHC above the threshold

---

### Contractual warranty

Warranty period

18 months