



### Main

Device short name	XCSL
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure ice/sleet proof indoor/outdoor

---

### Complementary

Line Rated Current	10 A
[Us] rated supply voltage	110 V AC
Actuator	Key
Contacts operation	Slow-break, break before make
Contacts type and composition	1 NO staggered 2 NC
Depth	1.73 in
Enclosure material	Metal
Height	7.64 in
Installation direction	Left actuator supply Front electromagnet connection
Key locking position	Front
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	3
Permissible voltage	$\leq 300$ V AC
Pilot light	LED orange
Type of connector	Mini 6 pins

---

### Environment

Ambient air temperature for operation	-13...158 °F
IP degree of protection	IP67
NEMA degree of protection	NEMA 1/2/3/4/12

---

---

Product certifications	CSA LR4408794 class 3211 03 CE UL listed file E164353 CCN NKCR
------------------------	--

---

**Ordering and shipping details**

---

Category	18488 - INDUSTRIAL APPS-NON-NEGOTIABLE-T
GTIN	00785901577232
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2000000000000002
Returnability	N
Country of origin	ID

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---