

Specifications







- Available capacities: 32GB, 64GB and 128GB*
- Up to 100MB/s (667X) read speed,
Up to 90MB/s (600X) write speed**
- 4K UHD and Full HD Video¹
- Class 10, App Performance Class 1 (A1)²
Video Speed Class 30 (V30)⁴,
UHS Speed Class 3 (U3)⁴
- SanDisk Memory Zone included³
- RescuePRO® Deluxe one year
media recovery software (download offer)⁵
- Lifetime limited warranty⁶



Terms and Conditions apply.



Set-up information: 32GB, 64GB and 128GB*

Product Name	Sales Item No.	Single Pack UPC	Master Carton UPC (SCC-14)
32GB SanDisk Extreme® PLUS microSDHC™ UHS-I Card with adapter	SDSQXBG-032G-GN6MA	619659155353 	60619659155355 
64GB SanDisk Extreme® PLUS microSDXC™ UHS-I Card with adapter	SDSQXBG-064G-GN6MA	619659155384 	60619659155386 
128GB SanDisk Extreme® PLUS microSDXC™ UHS-I Card with adapter	SDSQXBG-128G-GN6MA	619659154615 	60619659154617 

Details: 32GB, 64GB and 128GB*

	Weight	Dimensions (H x W x L)	Other
Individual Product (card)	0.01 lb. 4.54 g	0.43 x 0.59 x 0.04 in. 10.92 x 14.99 x 1.02 mm	<ul style="list-style-type: none"> • Master Carton Qty: 25 • Languages on Package: English, French, Italian, German, Spanish, Russian • Country of Origin: China or Taiwan • Warranty: Lifetime⁶ • Has main plug: N/A • Batteries required: N/A • Batteries included: N/A • Battery weight: N/A • Battery material: N/A • Battery capacity: N/A • Battery life: N/A
Individual Product (adapter)	0.01 lb. 4.54 g	1.25 x 0.94 x 0.08 in. 31.75 x 23.88 x 2.03 mm	
Single Package	0.03 lb. 14.30 g	6.00 x 4.00 x 0.26 in. 152.40 x 101.60 x 6.62 mm	
Packaging Paper	8 g		
Packaging Tray	1.70 g		
Total Packaging w/o product	9.70 g		
Master Package	0.97 lb. 440.51 g		

- Water Proof⁷
 Temperature Proof⁷
 Shock Proof⁷
 X-Ray Proof⁷

* 1GB=1,000,000,000 bytes. Actual user storage less

** Up to 100MB/s (667X) read speed; write speed up to 90MB/s (600X). Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes

¹ Compatible device required. 4K UHD (3840x2160) video support may vary based upon host device, file attributes, and other factors. See www.sandisk.com/HD

² Results may vary based on host device, app type and other factors

³ Download required. See www.sandisk.com/memoryzone

⁴ Video Speed Class 30 (V30), sustained video capture rate of 30MB/s, and UHS Speed Class 3 (U3) designate a performance option designed to support real-time video recording with UHS enabled host devices. See www.sdcard.org/consumers/speed

⁵ Registration required. Terms and conditions apply

⁶ See www.sandisk.com/wug

⁷ Card only: See www.sandisk.com/proof

SanDisk, RescuePRO and SanDisk Extreme are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. The microSD, microSDHC, microSDXC, SDHC and SDXC marks and logos are trademarks of SD-3C, LLC. Android is a trademark of Google Inc. The Android robot is reproduced or modified from work created and shared by Google and used according to terms described in the Creative Commons 3.0 Attribution License. Windows and the Windows logo are trademarks of the Microsoft group of companies. All other marks are the property of their respective owners.

© 2017 Western Digital Corporation. All rights reserved. Rev. 2/17

Western Digital Technologies, Inc. is the seller of record and licensee in the Americas of SanDisk® products.