

Basic

Brand Name: Acer
DVI: Yes
Environmentally Friendly: Yes
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Number of USB 2.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: Veriton X2640G
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Number of USB Ports: 8
Total Solid State Drive Capacity: 128 GB
VGA: Yes

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
TV Card: No

General Information

Brand Name: Acer
Manufacturer Part Number: DT.VMXEK.030
Manufacturer Website Address: <http://www.acer.co.uk>
Manufacturer: Acer, Inc
Product Line: Veriton
Product Name: Veriton X2640G Desktop Computer
Product Series: X2640G
Product Type: Desktop Computer

I/O Expansions

Number of PCI Express x1 Slots: 1
Number of PCI Express x16 Slots: 1
Number of Total Expansion Slots: 2

Input Devices

Keyboard Type: Physical Keyboard
Keyboard: Yes
Pointing Device Type: Mouse

Interfaces/Ports

Audio Line In: Yes
Audio Line Out: Yes
DVI: Yes
Modem (RJ-11): No
Network (RJ-45): Yes
Number of USB 2.0 Ports: 4
Number of USB 3.1 Gen 1 Ports: 4
Total Number of USB Ports: 8
VGA: Yes

Memory

Maximum Memory: 16 GB
Memory Card Reader: Yes
Memory Card Supported: SD
Memory Standard: DDR4-2133/PC4-17000
Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none">• DMI• GS• PC2001• Citrix ready• BSMI• VCCI• CE• FCC• CB
Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none">• Veriton X2640G Desktop Computer• USB Keyboard• USB Mouse

Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

Physical Characteristics

Depth:	354 mm
Height:	265 mm
Width:	100 mm

Power Description

Maximum Power Supply Wattage:	220 W
----------------------------------	-------

Processor & Chipset

64-bit Processing:	Yes
Cache:	3 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Direct Media Interface:	8 GT/s
Hyper-Threading:	Yes
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Dual-core (2 Core)
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3
vPro Technology:	No

Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Software Included:	Microsoft Office trial

Storage

Number of Solid State Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Solid State Drive Configuration:	1 x 128 GB
Solid State Drive Interface:	Serial ATA/300
Total Solid State Drive Capacity:	128 GB