

## Basic

Brand Name: Acer  
DVI: Yes  
Environmentally Friendly: Yes  
Graphics Controller: Intel  
Manufacturer:  
Graphics Controller Model: HD Graphics 530  
Graphics Memory Accessibility: Shared  
Graphics Memory Technology: DDR4 SDRAM  
Number of USB 2.0 Ports: 4  
Operating System Architecture: 64-bit  
Operating System Platform: Windows  
Operating System: Windows 10 Pro  
Optical Drive Type: DVD-Writer  
Processor Manufacturer: Intel  
Processor Model: i5-6400  
Processor Speed: 2.70 GHz  
Processor Type: Core i5  
Product Family: Veriton X2640G  
Product Type: Desktop Computer  
Standard Memory: 4 GB  
Total Number of USB Ports: 8  
Total Solid State Drive Capacity: 128 GB  
VGA: Yes

## Display & Graphics

Graphics Controller: Intel  
Manufacturer:  
Graphics Controller Model: HD Graphics 530  
Graphics Memory Accessibility: Shared  
Graphics Memory Technology: DDR4 SDRAM  
TV Card: No

## General Information

Brand Name: Acer  
Manufacturer Part Number: DT.VMXEK.032  
Manufacturer Website Address: <http://www.acer.co.uk>  
Manufacturer: Acer, Inc  
Product Line: Veriton  
Product Name: Veriton X2640G Desktop Computer  
Product Series: X2640G  
Product Type: Desktop Computer

## I/O Expansions

Number of PCI Express x1 Slots: 1  
Number of PCI Express x16 Slots: 1  
Number of Total Expansion Slots: 2

## Input Devices

Keyboard Type: Physical Keyboard  
Keyboard: Yes  
Pointing Device Type: Mouse

## Interfaces/Ports

Audio Line In: Yes  
Audio Line Out: Yes  
DVI: Yes  
Modem (RJ-11): No  
Network (RJ-45): Yes  
Number of USB 2.0 Ports: 4  
Number of USB 3.1 Gen 1 Ports: 4  
Total Number of USB Ports: 8  
VGA: Yes

## Memory

Maximum Memory: 16 GB  
Memory Card Reader: Yes  
Memory Card Supported: SD  
Memory Standard: DDR4-2133/PC4-17000  
Memory Technology: DDR4 SDRAM  
Standard Memory: 4 GB

## Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none"><li>• DMI</li><li>• GS</li><li>• PC2001</li><li>• Citrix ready</li><li>• BSMI</li><li>• VCCI</li><li>• CE</li><li>• FCC</li><li>• CB</li></ul>
Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none"><li>• Veriton X2640G Desktop Computer</li><li>• USB Keyboard</li><li>• USB Mouse</li></ul>

## Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

## Physical Characteristics

Depth:	354 mm
Height:	265 mm
Width:	100 mm

## Power Description

Maximum Power Supply Wattage:	220 W
----------------------------------	-------

## Processor & Chipset

64-bit Processing:	Yes
Cache:	6 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Direct Media Interface:	8 GT/s
Maximum Turbo Speed:	3.30 GHz
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Quad-core (4 Core)
Processor Manufacturer:	Intel
Processor Model:	i5-6400
Processor Speed:	2.70 GHz
Processor Type:	Core i5

## Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

## Storage

Number of Solid State Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Solid State Drive Configuration:	1 x 128 GB
Solid State Drive Interface:	Serial ATA/300
Total Solid State Drive Capacity:	128 GB