

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002081001](#)
Status: **Active**
Overview: MLX™ Power Connectors
Description: MLX™ Female Crimp Terminal 42024, 14-20 AWG, Reel, Brass, Tin (Sn) Plating

Documents:

[3D Model](#) [Product Specification TS-42022-0001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-42022-0001-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>42024</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>MLX™ Power Connectors</u>
Packaging Alternative	<u>02-08-1002 (Loose)</u>
Product Name	MLX™
UPC	800753615878

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.344/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	42024-1A1
--------------------	-----------

Reference - Drawing Numbers

Product Specification	PS-42022-0001-001, TS-42022-0001-001
Sales Drawing	SD-42024-****



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

[42024 Series](#)