

Electronic housing - UCS 145-125-F-GD 7035 - 2203332

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Complete housing for PCBs, can be positioned flexibly; includes housing half shells, side panels closed, adhesive domes for PCB attachment, screws for housing and PCB attachment; light gray housing with turquoise-green corner inlays

Why buy this product

- ✓ High degree of application flexibility, thanks to the modular housing design
- ✓ Flexible PCB attachment, adapts to virtually all form factors
- ✓ Practical customization options
- ✓ Reduced logistics outlay, thanks to components which are compatible with one another



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 STK |
| GTIN |  4 055626 404448 |
| GTIN | 4055626404448 |
| Weight per Piece (excluding packing) | 208.260 g |
| Custom tariff number | 39269097 |
| Country of origin | Germany |

Technical data

General

| | |
|------------------|------------------|
| Housing type | Complete housing |
| Housing material | PC |
| Color (RAL) | gray (7035) |

Ambient conditions

| | |
|---|--|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Ambient temperature (operation) | -40 °C ... 100 °C (depending on power dissipation) |

Dimensions

Electronic housing - UCS 145-125-F-GD 7035 - 2203332

Technical data

Dimensions

| | |
|--------|--------|
| Width | 145 mm |
| Height | 125 mm |
| Depth | 47 mm |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27180506 |
| eCl@ss 8.0 | 27182702 |
| eCl@ss 9.0 | 27182702 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC001031 |
|----------|----------|

Accessories

Accessories

Screwdriver tools

Screwdriver - SF-TXH 10X80 - 1200149



Screwdriver, Torx® with bore hole, TX 10 x 80, two-component handle