

165 iS PZ/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Pozidriv/slotted) , PZ/S # 2 x 100 mm
VDE Insulated screwdriver



EAN	4013288160287	Dimension:	205x37x37 mm
Code:	05006466001	Weight:	82 g
Article-No.		Country of origin:	CZ
		Customs tariff no.:	82054000

- Insulated VDE blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Reduced shaft diameter: combination profile - Pozidriv / slotted

Wera VDE screwdrivers with multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Combination profile - slotted and Pozidriv* particularly for jobs on terminal blocks, fuse boxes, switches and relays. Individually tested in water bath at 10,000 volts for secure work at the permissible voltage of 1,000 volts. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.