

Flat gasket - HC-B24-SG-RBK - 1407705

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Replacement flat gasket, for HEAVYCON EVO panel mounting base type B24



Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 046356 777995
GTIN	4046356777995
Weight per Piece (excluding packing)	7.500 g
Custom tariff number	40169300
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


General

Material	NBR
Assembly instructions	For HC-EVO-B24.....BK housing

Drawings

Flat gasket - HC-B24-SG-RBK - 1407705

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	23071590
eCl@ss 9.0	27430319

ETIM

ETIM 3.0	EC000796
ETIM 4.0	EC000437
ETIM 5.0	EC001181
ETIM 6.0	EC001181

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39131608

Approvals

Approvals

Approvals


EAC

Ex Approvals

Flat gasket - HC-B24-SG-RBK - 1407705

Approvals

Approval details

EAC		7500651.22.01.00246
-----	---	---------------------

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>