

Thermal transfer printer - THERMOMARK ROLL - 5146477

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Thermal transfer printer for material off the roll

Why buy this product

- ✓ Maintenance-free operation with proven thermal transfer printing technology
- ✓ Easy to control with the CLIP PROJECT software
- ✓ For all labels and shrink sleeves
- ✓ Easy operating concept based on user-friendly touch screen entry
- ✓ High-quality, fast labeling
- ✓ The THERMOMARK ROLL can print markers supplied in roll format for terminal, conductor, cable, and device marking applications
- ✓ USB and Ethernet connections



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 528566
GTIN	4046356528566
Weight per Piece (excluding packing)	5,875.500 g
Custom tariff number	84433210
Country of origin	Germany

Technical data

General

Interface	10/100 Mbps Ethernet
	USB 2.0
Weight	3.80 kg

Dimensions

Length	320.00 mm
Height	189.00 mm

Thermal transfer printer - THERMOMARK ROLL - 5146477

Technical data

Dimensions

Width	253.00 mm
-------	-----------

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	24010402
eCl@ss 4.1	24010402
eCl@ss 5.0	19020207
eCl@ss 5.1	19020207
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001672
ETIM 5.0	EC001672
ETIM 6.0	EC001672

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212108

Approvals

Approvals

Thermal transfer printer - THERMOMARK ROLL - 5146477

Approvals

Approvals

UL Listed / cUL Listed / IECEE CB Scheme / EAC / KC / CCC / EAC / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
IECEE CB Scheme		http://www.iecee.org/	DK-5163-A1-UL
EAC			EAC-Zulassung
KC		http://rra.go.kr/eng2/index.jsp	KCCREIPCK-FL5146477
CCC		http://www.china-certification.com	2012010904577464
EAC			7500651.22.01.00240
cULus Listed			

Accessories

Accessories

Thermal transfer printer - THERMOMARK ROLL - 5146477

Accessories

Documentation

Manual - UM IA THERMOMARK ROLL - 2910897

Manual

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, Width: 110 mm, Color: blue

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, Width: 110 mm, Color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, Width: 110 mm, Color: red

Thermal transfer printer - THERMOMARK ROLL - 5146477

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon for EMLHT high-temperature labels, length: 300 m, width: 110 mm, ink color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color white

Thermal transfer printer - THERMOMARK ROLL - 5146477

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, Width: 110 mm, Color: black

Ink ribbon - TM-RIBBON 110-TC/TR WH - 1014402



Ink ribbon, Color: white

Mounting material

Replacement part - TC/TR-PACKAGE WITH FOAM - 0801804

Replacement part

Locking - TR-MARGIN STOP - 0801810



Locking

Pressure roller - TR-PRESSURE ROLLER DR4-50 - 0801800

Pressure roller



Pressure roller - TR-PRESSURE ROLLER STANDARD - 0801802

Pressure roller



Thermal transfer printer - THERMOMARK ROLL - 5146477

Accessories

Demolition plate - TR-TEAR OFF PLATE - 0801803



Demolition plate

Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Printing system accessories

Thermal transfer printer - THERMOMARK ROLL - 5146477

Accessories

Cutter - THERMOMARK ROLL-CUTTER - 5146422



Cutter, for the THERMOMARK ROLL, cutter width: 110 mm, suitable for: labels, continuous media up to 110 mm wide, PMM continuous media up to 50.1 mm in diameter, TMT continuous media, and EMT (EX15)R

Cutter - THERMOMARK ROLL-CUTTER/P - 5146435



Perforation cutter, for the THERMOMARK ROLL, cutter width: 60 mm, suitable for: WMS continuous media up to 25.8 mm in diameter, TMT continuous media, and EMT (EX15)R

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Transport case - TL CASE - 0800613



Transport case for THERMOMARK printer, rounded profile case with aluminum frame

Thermal transfer printer - THERMOMARK ROLL - 5146477

Accessories

Cart for printer - TL CASE TROLLY - 0803337



Trolley for the transport cases for THERMOMARK LINE and THERMOMARK ROLL X1

Accessories - THERMOMARK-CP - 5145371



Cleaning pen, for thermal transfer printers
