


## Model 3560, 3562, 3564 & 4690 Connector Test Adapters Banana Jack To #12, 16, 20 & 22 Socket



### FEATURES:

- An ideal test adapter for testing multi pin connectors.
- Flexible tip allows easy access to adjacent pins.
- Use 3560 to test # 20 contact pins  $\phi .040$
- Use 3562 to test #16 contact pins  $\phi .063$
- Use 3564 to test #12 contact pins  $\phi .093$
- Use 4690 to test #22 contact pins  $\phi .030$

### MATERIALS:

Upper Conn.: Banana Jack Body

Material: Brass.

Finish: Bright Tin plated

Insulation: Polyvinyl chloride (PVC).

Operating Temperature:  $+55^{\circ}\text{C}$  ( $+122^{\circ}\text{F}$ .) Max.

Marking: "POMONA ELECTRONICS CALIF. 3560", 3562", 3564" & 4690".

Lower Conn: "MS" Style Contact, #20 Socket (3560), #16 Socket (3562), #12 Socket (3564) & #22 Socket (4690).

Material: Copper Alloy

Finish: Gold over copper plate

### RATINGS:

Operating Voltage: 2500 VDC

Operating Temperature:  $50^{\circ}\text{C}$ . ( $+122^{\circ}\text{F}$ .) Max..

Current: 7.5 Amperes (3560), 13 Amperes (3562), 23 Amperes (3564), 5 Amperes (4690)

**ORDERING INFORMATION:** Model 3560-\*, 3562-\*, 3564-\*, 4690-\*

\*=Color, -0 Black, -2 Red

Ordering Example 3560-2 Adapter Color is Red.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

Sales: 909-469-2900 Fax: 909-629-3317  
Technical Assistance: 800-241-2060

PomonaACCESS 90886 (800) 444-6785 or (909) 469-2991  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)