

## DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Plug component, Nominal current: 3 A, Number of positions: 16, Pitch: 2.54 mm, Color: jet black

### Why buy this product



### Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 096768
GTIN	4046356096768
Weight per Piece (excluding packing)	12.070 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### General

Housing material	Polyamide
Color	black

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
---------------------------------	---

#### Dimensions

Length	37.1 mm
Width	35.6 mm
Pitch	2.54 mm

#### Technical data

Connection in acc. with standard	CUL
Nominal voltage $U_N$	60 V

# DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

## Technical data

### Technical data

Nominal current $I_N$	2 A
Indicator1	CUL1
Flammability rating according to UL 94	V0
Number of positions	16

### Standards and Regulations


Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


## Drawings

Dimensional drawing



A=35.6 mm

Circuit diagram



## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

### ETIM

ETIM 3.0	EC001121
----------	----------

# DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

## Classifications

### ETIM

ETIM 4.0	EC002637
ETIM 5.0	EC002638
ETIM 6.0	EC002638

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals


### Approvals


#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 118976
Nominal current IN		2 A	
Nominal voltage UN		30 V	

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 118976
Nominal current IN		2 A	
Nominal voltage UN		30 V	

EAC		EAC-Zulassung
-----	---	---------------

## DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

### Approvals

cULus Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

### Accessories

#### Accessories

##### Filler plug

Printed-circuit board connector - HBUS-B SET BK - 2278173



Set of 3 caps, for protecting unused DIN rail bus connectors, simply snap on to fit

Electronic housing - BSL-2,54/16-ST 40CM - 2202938



Cable bridge for cross-DIN-rail connection of the HBUS connector

Electronic housing - BSL2-2,54/16-ST - 2201281



Cable bridge for cross-DIN-rail connection of the HBUS connector

Power plug - SL2-2,54/16-ST - 2896348



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm<sup>2</sup>, 500 mm long, male contacts

## DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

### Accessories

Power plug - BL2-2,54/16-ST - 2896335



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm<sup>2</sup>, 500 mm long, female contacts

---

### Necessary add-on products

PSTD 0,65X0,65/9-2,54 - 2200700



Pin strip (horizontal)

---

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>