

Electronic housing - BC 107,6 UT HBUS KMGY - 2202951

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Installation component housing, Color: light gray

Why buy this product

- Item is from the BC product range
- Conforms to DIN EN 43880
- Tool-free mounting
- Available in overall widths from one to nine width units (17.8 mm ... 161.6 mm)
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall
- Optional with bus connector for DIN rail mounting

Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	
GTIN	4055626282114
Weight per Piece (excluding packing)	46.400 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Housing type	Installation component housing
Housing material	Polycarbonate
Color	light gray

Ambient conditions

Electronic housing - BC 107,6 UT HBUS KMGY - 2202951

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Length	89.7 mm
--------	---------

Technical data

Flammability rating according to UL 94	V0
--	----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031

UNSPSC

UNSPSC 13.2	31261501
-------------	----------

Approvals

Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	--	---	---------------

Electronic housing - BC 107,6 UT HBUS KMGY - 2202951

Approvals

EAC		EAC-Zulassung
-----	--	---------------

Accessories

Accessories

Fiber optics

Component housing - HS LC-V-D3/ R2XC1-5,08 - 2202311



Fiber optics Can be used for the BC housing range (housing must be processed), Color: transparent

Component housing - HS LC-V-D3/ R3XC1-5,08 - 2202312



Fiber optics Can be used for the BC housing range (housing must be processed), Color: transparent

Necessary add-on products

Components of electronic housing - BC 107,6 OT U11 KMGY - 2896076



Installation component housing, Upper part, Cross connection: Component housing, Color: light gray, Width: 107.6 mm, Constructional height: 62.2 mm

Upper part of housing - BC 107,6 OT U22 KMGY - 2896089



Installation component housing, Upper part, Color: light gray, Width: 107.6 mm, Constructional height: 62.2 mm

Electronic housing - BC 107,6 UT HBUS KMGY - 2202951

Accessories

Electronic housing - RPI-BC 107,6 DEV-KIT KMGY P10 - 2202875



DIN rail housing for Raspberry Pi computers (suitable for Raspberry Pi A+, B+, B2, B3); set consisting of upper part and PCB holder; housing according to DIN 43880

Additional products

DIN rail bus connectors - HBUS 107,6-16P-1S BK - 2896306



Plug component, Nominal current: 3 A, Number of positions: 16, Pitch: 2.54 mm, Color: jet black