

EDIFIER®

M1550

The M1550, 5.1 speaker system by Edifier is an efficient mini home theatre solution, or simply a speaker system for optimal surround sound. The wooden encased subwoofer provides rich sound while the volume is controlled with ease via the wired remote controller. The 3.5mm jacks allow the ability for both stereo input signal and 5.1 channel input signal.



26
watts
R.M.S
TOTAL POWER OUTPUT

Features

- Mini home theatre/surround sound 5.1 multi-media speaker system
- Wooden MDF subwoofer enclosure
- Master volume control, green indicator, stand-by option, and line-out for headphone all included on wired remote controller
- 3.5mm jacks accept both stereo input signal and 5.1 channel input signal

Specifications

Power output	: RMS 3W x 4 +RMS 4W + RMS 10W
Signal to noise ratio	: ≥ 85 dB
Input sensitivity	: Satellites: 350mV \pm 50mV Subwoofer: 80mV \pm 20mV
Input type	: Auxilliary, Headphone Jack
Midrange and Bass unit	: 2 inch x 3½ inch / 4 inch
EAN code	: 6923520265046 (UK)



Disclaimer: All specifications are subject to change without notice

www.edifier.com

A Passion for Sound