

SATA SSD AS330

Apacer AS330

Reliable Solution for Computer System

Optimization

Apacer AS330 is a solid state drive (SSD) in standard 2.5" SATA form factor. Designed in SATA 6 Gb/s interface, the drive can deliver outstanding performance up to 520 MB/s data transfer speed, highly suitable to serve as operating system boot drive or storage media of important data. The mechanical design of AS330 conforms to the latest requirements of SATA 6.0 Gbps interface. Hence, power efficiency wise, AS330 supports SATA power management modes which greatly cut power consumptions to make it an environmental and economical storage drive than traditional hard disk drives.

In terms of reliability, AS330 supports wear leveling, S.M.A.R.T., NCQ command, and ECC engine correcting up to 72bit per 1KB data. With the advantages of performance and reliability mentioned above, AS330 is proved to be the best companion for PC and laptop upgrade.


Features:

- SATA 6.0 Gb/s interface compliance
- Outstanding read/write performance
- Supports SATA Power Management
- Powerful ECC engine correcting up to 72bit/1KB
- Supports S.M.A.R.T. commands
- Supports TRIM commands



Applications

- PC/NB for general storage
- Operating system boot drive for PC/NB
- Network servers
- Industrial PCs
- Graphic and video applications
- Kiosk, POS and automation.
- Multimedia
- Gaming



SATA SSD AS330



General Product Specifications

Specifications			
Interface	SATA 6.0 Gb/s interface		
SATA 6.0 Gbps Burst Speed	600 MB/s		
Capacity ¹	120 GB, 240 GB, 480 GB, 960 GB		
Performance ² (Unit: MB/s)	Capacity	Read	Write
	120 GB	495	385
	240 GB	515	475
	480 GB	520	480
	960 GB	520	485
Form Factor	2.5 inch		
NAND Flash Media	TLC		
ECC	Up to 72bit/1KB		
MTBF	1,000,000 hours (approx.)		
Operating Voltage	5V ± 5%		
Power consumption ³ (Unit: mA)	Active	1,200	
	Idle	150	
Dimension	100.10mm(L) x 69.85mm(W) x 7.00mm(H)		
Reliability Features	S.M.A.R.T, TRIM, Wear-leveling		
Temperature	Operating	0°C to 70°C	
	Storage	-40°C to 85°C	
Humidity	RH 90% under 40°C		
Shock ⁴	500G/2ms		
Vibration ⁴	80 – 2000Hz/20G		
Acoustic	0dB		
Warranty	3 years		
Package Content	Retail package		
Certifications	RoHS, CE, FCC		

Global Offices

Taiwan (HQ)

Apacer Technology Inc.
1F., No.32, Zhongcheng Rd.,
Tucheng Dist., New Taipei City
Taiwan, R.O.C
Tel: +886-2-2267-8000
Fax: +886-2-2267-2261
amtsales@apacer.com

U.S.A

Apacer Memory America, Inc.
46732 Lakeview Blvd., Fremont,
CA 94538
Tel: 1-408-518-8699
Fax: 1-510-249-9568
sa@apacer.com

Japan

Apacer Technology Corp.
5F, Matsura Bldg., Shiba, Minato-Ku
Tokyo, 105-0014, Japan
Tel: 81-3-5419-2668
Fax: 81-3-5419-0018
jpservices@apacer.com

Europe

Apacer Technology B.V.
Science Park Eindhoven 5051 5692
EB Son,
The Netherlands
Tel: 31-40-267-0000
Fax: 31-40-267-0000#6199
sale@apacer.nl

China

**Apacer Electronic (Shanghai)
Co., Ltd**
Room D, 22/FL, No.2, Lane 600,
Jieyun Plaza, Tianshan RD,
Shanghai, 200051, China
Tel: 86-21-6228-9939
Fax: 86-21-6228-9936
sales@apacer.com.cn

India

Apacer Technologies Pvt Ltd
Unit No.201, Brigade Corner,
7th Block Jayanagar, Yediyur Circle,
Bangalore – 560082, India
Tel: 91-80-4152-9061
Fax: 91-80-4170-0215
sales.india@apacer.com

¹ Unformatted. Theoretically, 1GB=1,000,000,000 Bytes. Under operating systems, the capacity might appear to be less than the theoretical capacity because the calculation in OS is based on 1 GB = 1024 MB / 1MB =1024KB and a minority of the capacity is reserved for maintenance purposes.

² Performance results may vary from flash configurations or host system settings. Test results are based on ATTO platform.

³ Power consumption was measured at 5.0V and for 960 GB capacity only. The results may vary from flash configurations or host system settings.

⁴ Shock and vibrations are subject to change without notice.

SATA SSD AS330

Ordering Information

Capacity	Bulk	Distributor/Retailer
120 GB	AP120GAS330	AP120GAS330-1
240 GB	AP240GAS330	AP240GAS330-1
480 GB	AP480GAS330	AP480GAS330-1
960 GB	AP960GAS330	AP960GAS330-1

Revision History

Version	Description	Date
1.0	Official release	9/18/2015

Apacer Technology Inc.

1F., No.32, Zhongcheng Rd., Tucheng Dist., New Taipei City
Tel: +886-2-2267-8000 Fax: +886-2-2267-2261
www.apacer.com

Copyright ©2015 Apacer Technology Inc. All Rights Reserved.
Information in this document is subject to change without prior notice.
Apacer and the Apacer logo are trademarks or registered trademarks of Apacer Technology Inc. Other brands, names, trademarks or registered trademarks may be claimed as the property of their respective owners.