

Brand Name: Lenovo
Colour: Black
DisplayPort: Yes
Energy Star: Yes
Environmentally Friendly: Yes
Form Factor: Small Form Factor
HDMI: Yes
Keyboard Localization: English (UK)
Number of DisplayPort Outputs: 1
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 6
Operating System Platform: Windows
Operating System: Windows 10 Home
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-7100
Processor Speed: 3.90 GHz
Processor Type: Core i3
Product Family: V520S-08IKL
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Number of USB Ports: 8
Total Solid State Drive Capacity: 128 GB
VGA: Yes

General Information

Brand Name: Lenovo
Manufacturer Part Number: 10NM003BUK
Manufacturer Website Address: <http://www.lenovo.com/uk/en/>
Manufacturer: Lenovo Group Limited
Product Model: 10NM003BUK
Product Name: V520S-08IKL 10NM003BUK Desktop Computer
Product Series: V520S-08IKL
Product Type: Desktop Computer

Input Devices

Keyboard Localization: English (UK)

Interfaces/Ports

DisplayPort: Yes
HDMI: Yes
Number of DisplayPort Outputs: 1
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 6
Total Number of USB Ports: 8
VGA: Yes

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Energy Star: Yes
Environmental Certification: ENERGY STAR 6.1
ErP Lot 3
GREENGUARD
RoHS
Environmentally Friendly: Yes
Features: Security Slot
Package Contents:

- V520S-08IKL 10NM003BUK Desktop Computer
- Keyboard
- Mouse
- External Cables

Physical Characteristics

Colour: Black
Depth: 345.4 mm
Form Factor: Small Form Factor
Height: 88.9 mm
Weight (Approximate): 4.75 kg
Width: 289.6 mm

Power Description

Input Voltage: 120 V AC
230 V AC

Processor & Chipset

Processor Generation: 7th Gen
Processor Manufacturer: Intel
Processor Model: i3-7100
Processor Speed: 3.90 GHz
Processor Type: Core i3

Software

Operating System Platform: Windows
Operating System: Windows 10 Home

Storage

Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM
Total Solid State Drive Capacity: 128 GB