



## Display

### Screen Size (Inch)

27

### Active Display Size (HxV) (mm)

597.6mm x 336.15mm

### Panel Type

TN

### Brightness (Min)

250cd/m<sup>2</sup>

### Dynamic Contrast Ratio

Mega ∞

### Response Time

1 (GTG)

### Colour Support

16.7M

### Refresh Rate

60Hz

### Flat / Curved

Flat

### Aspect Ratio

16:9

### Brightness (Typical)

300cd/m<sup>2</sup>

### Contrast Ratio Static

1000:1(Typ.)

### Resolution

1920 x 1080

### Viewing Angle (Horizontal/Vertical)

170°/160°

### Colour Gamut (NTSC 1976)

72%

## General Feature

### Samsung MagicAngle

Yes

### Samsung MagicBright

Yes

**Samsung MagicUpscale**

Yes

**Eye Saver Mode**

Yes

**Game Mode**

Yes

**Windows Certification**

Windows 10

**Eco Saving Plus**

Yes

**Flicker Free**

Yes

**Image Size**

Yes

[SHOW MORE SPECS](#) —**Interface****Wireless Display**

No

**DVI**

No

**Display Port**

No

**USB Display**

No

**Headphone**

No

**D-Sub**

1EA

**Dual Link DVI**

No

**HDMI**

1EA

**Audio In**

No

**USB Hub**

No

**Audio****Speaker**

No

**USB Sound Bar (Ready)**

No

**Operation Conditions****Temperature**

10~40°C

**Humidity**

10~80 (non-condensing)

**Design****Color**

Black

**Stand Type**

Simple

**Tilt**

-2°(±2.0°) ~ 20°(±2.0°)

**Wall Mount**

75.0 x 75.0 mm

**Power****Power Supply**

AC 100~240V

**Power Consumption (Max)**

35W

**Power Consumption (Typ)**

32W

**Power Consumption (DPMS)**

0.3 (Typ.)

**Power Consumption (Off Mode)**

0.3 (Max)

**Type**

External Adaptor

---

**Dimension****Set Dimension with Stand (WxHxD)**

643.4 x 463.1 x 200.7mm

**Set Dimension without Stand (WxHxD)**

643.4 x 385.3 x 95.1mm

**Package Dimension (WxHxD)**

717.0 x 155.0 x 459.0mm

---

**Weight****Set Weight with Stand**

4.9kg

**Set Weight without Stand**

4.50kg

**Package Weight**

6.55kg

---

**Accessory****Power Cable**

Yes

**Power Cable Length**

1.5m

**HDMI Cable**

Yes

---