



FEATURES

- USB flash disk and SD card playback
- 6 1/2 inch bass and 3 inch mid-range drivers
- Integrated side control panel makes system adjustments easy and convenient
- Six buttons for audio source selection, previous/next track, play/pause and volume up/down
- USB/SD card playback supports breakpoint memory function
- Able to memorize mode and volume
- Support USB/SD card folders change
- Universal 100V-240V power supply

SPECIFICATIONS

Power output: R/L: RMS 12W× 2 SW: 24W
 Signal to noise rate: ≥ 85dBA
 Frequency response: 50Hz~20KHz (±8dB)
 Input sensitivity: R/L: 400mV±50mV SW: 70mV±20mV
 Input type: AUX/USB/SD card
 Bass unit: 6 1/2 inch(178mm)
 Mid-range unit: 3 inch(78mm)
 Treble unit: Φ 10mm

ORDERING DETAILS

EAN:
6923520264841

Color:
Black

*All specifications are subject to change without notice