

Acer K242HL(UM.FX3EE.002)

Acer K242HL - LED monitor - 24" - 1920 x 1080 Full HD (1080p) - TN - 250 cd/m² - 5 ms - HDMI ,DVI ,VGA - black



The Acer K2 series monitors are affordable display solutions for everyday PC usage. They offer hassle-free usability without compromising image quality. The intelligent design brings together a multitude of connection ports, superb performance.

Key Selling Points

24"LED-backlit LCD monitor
Full HD 1080p (1920 x 1080)
250nits brightness
100000000:1 contrast ratio

Main Specifications

Product Description	Acer K242HL - LED monitor - 24"
Device Type	LED-backlit LCD monitor - 24"
Energy Class	Class A
Energy Consumption per Year	34 kWh
Power Consumption (On mode)	23 W
Panel Type	TN
Aspect Ratio	Widescreen - 16:9
Native Resolution	Full HD (1080p) 1920 x 1080 at 60 Hz
Brightness	250 cd/m ²
Contrast Ratio	100000000:1 (dynamic)
Response Time	5 ms (On/Off)
Colour Support	16.7 million colours
Input Connectors	HDMI ,DVI ,VGA
Display Position Adjustments	Tilt
Colour	Black
Dimensions (WxDxH) - with stand	56.7 cm x 20.7 cm x 42.19 cm
Weight	3.57 kg
Environmental Standards	ENERGY STAR Qualified
Compliant Standards	MPR II
Manufacturer Warranty	2 years warranty

Extended Specification

General

Display Type	LED-backlit LCD monitor / TFT active matrix
Energy Class	Class A
Energy Consumption per Year	34 kWh

Power Consumption (On mode)	23 W
Diagonal Size	24"
Panel Type	TN
Aspect Ratio	Widescreen - 16:9
Native Resolution	Full HD (1080p) 1920 x 1080 at 60 Hz
Brightness	250 cd/m ²
Contrast Ratio	100000000:1 (dynamic)
Colour Support	16.7 million colours
Response Time	5 ms (On/Off)
Horizontal Viewing Angle	170
Vertical Viewing Angle	160
Backlight Technology	LED backlight
Features	HDCP,Acer EcoDisplay,Acer Adaptive Contrast Management (ACM),High Frame Rate Control (Hi-FRC),ComfyView
Colour	Black
Dimensions (WxDxH)	56.7 cm x 20.7 cm x 42.19 cm - with stand
Weight	3.57 kg

Connectivity

Interfaces	DVI (HDCP) VGA HDMI
------------	---------------------------

Mechanical

Display Position Adjustments	Tilt
Tilt Angle	-5/+25
Flat Panel Mount Interface	100 x 100 mm

Miscellaneous

Features	VESA interface support
Cables Included	1 x VGA cable
Compliant Standards	MPR II

Power

Voltage Required	AC 120/230 V (50/60 Hz)
Power Consumption Operational	20.09 Watt
Power Consumption Stand by	0.45 Watt
Power Consumption (Off Mode)	0.35 Watt
On / Off Switch	No

Dimensions &Weight

Dimensions &Weight Details	Without stand - width:56.7 cm - depth:5.2 cm - height:33.59 cm - weight:3.1 kg With stand - width:56.7 cm - depth:20.7 cm - height:42.19 cm - weight:3.57 kg
----------------------------	---

Environmental Standards

ENERGY STAR Qualified Yes

Manufacturer Warranty

Service & Support Limited warranty - 2 years

What's in the box

Acer K242HL
VGA cable

Product data is provided by CNET, we do not warrant the accuracy and completeness of the material contained in this data sheet