

WIRELESS KITS

4CHN Recorder

With 4MP Cameras



CODE	NO. OF 4MP CAMERAS CHOOSE BETWEEN	NVR CHN	HDD SIZE CHOOSE BETWEEN
KIT-WIFI-4-1TB-D	2	4	1TB, 2TB, 4TB
KIT-WIFI-5-1TB-D	4	4	1TB, 2TB, 4TB
KIT-WIFI-6-1TB-D	8	4	1TB, 2TB, 4TB

360° 4CHN Panoramic Recorder



4x4 QUAD View



SPECIFICATION

Model	360° Panoramic Recorder • H.265
IP Video Input	4 CH x 720P/960P/1080P/3M/4M/5M/8M,RJ45 Interface
Switch	No
HDMI Output	1 CH, HDMI; Resolution:1920x1080P/60Hz; 4K/30Hz
VGA Output	No
Video Compression	H.265, H.264
Recording / Playback	4ch*720P/1080P/3M/4M/5M/8M recording 4ch*1080P/720P playback, 1ch*4M/5M/4M/3M playback
Video Resolution	720P, 960P, 1080P, 3M, 4M, 5M, 8M Recording
Frame Rate	PAL: 25 fps; NTSC: 30 fps
Video Bitrate	256 Kbps - 12.0 Mbps(@8M); 10.0Mbps(@5M); 5.0Mbps(@1080P)
Stream Type	Audio/Video, Variable Rate(VBR), Constant Bit Rate(CBR)
Dual-Stream	Support
Audio Compression	G.711
Storage Type	1 * SATA Interface
Storage Capacity	6TB (Max)
Backup	USB Backup
Network Interface	RJ45 10M /100M Internet Interface
USB Interface	2 * USB2.0 Interface(Support Upgrade,Backup,Mouse)
PTZ	1 * RS485 Interface
Temperature	-10°C - 55°C
Operation System	Embedded Linux Operation System
Device Control	Remote Control & Mouse
Power Input	DC +12 V / 2.0A

360° View



360-PAN4R-1TB/ 2TB/4TB/6TB

FEATURES

- Auto connects to cameras
- Support multi-language version
- Support multiple remote monitoring including mobile tablet and PC and free CMS

Wi-Fi 4MP Vandal



Model	WIFI4MP-VANDAL-D
Sensor	1/3" Progressive Scan Sensor
Resolution	4.0MP 1080P
Minimum illumination	Color: 0.1 Lux B/W: 0.05 Lux
Lens	4/6mm
OSD	Date Time & Title
White Balance	Auto
Day&Night	IR cut filter with auto switch
3D-DNR	Auto
Mirror/Flip	On / Off
Smart Stream	Main Stream: 2592x1520 Sub Stream: 720x576
S/N	> 39.1 Db
Interface	RJ45 / WIFI 802.11b/g/n
Working Temperature/Humidity	-20°C to +60°C / 20% to 90% RH
Power Input	DC12V-1A
Power consumption	≤6W
Size	100(D)*80(H)mm
Weight	500g

WIFI4MP-VANDAL-D

FEATURES

- High definition image quality
- Plug-play
- Wireless
- Easy installation and operation
- Save on installation costs
- P2P
- Support Android/IOS/PC remote