


EMI Filters, Three Phase, FLLD4-TH, 530 VAC, 64 A, 160x125x125mm



Dimensions	
L	160mm NOM
W	125mm NOM
H	125mm NOM
L1	100mm NOM
W1	137.5mm NOM
W2	153mm NOM
J	35mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M10

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Weight:	2.3 kg

General Information	
Style:	Chassis Mount
Series:	FLLD4-TH
Description:	EMI Filter, Chassis Mount, Compact
Features:	High Performance
RoHS:	Yes

Specifications	
Voltage AC:	530/305 VAC
Rated Frequency:	50-60 Hz
Current:	64 A (50C)
Rated Temperature:	50C
Temperature Range:	-25/+100C
Climate Category:	25/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Power Loss:	18 W (25C 50 Hz)
Leakage Current:	11 mA