

Aluminum Electrolytic, 85C, ALC10, 470 uF, 20%, 450 V, -40/+85C



Dimensions	
D	35mm +1mm
L	50mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Weight:	70 g
Sleeving:	Yes
Packaging:	Bulk
Packaging Quantity:	100

General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALC10
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
Notes:	Dimensions D And L Include Sleeving

Specifications	
Capacitance:	470 uF
Capacitance Tolerance:	20%
Voltage DC:	450 VDC, 495 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	15000 Hrs (Rated Voltage And Ripple Current At 85C), 24000 Hrs (Rated Voltage At 85C)
Resistance:	252 mOhms (100Hz 20C), 155 mOhms (10kHz 20C)
Current:	2.43 Amps (100Hz 85C), 4.03 Amps (10kHz 85C)
Leakage Current:	1269 uAmps (5min 20C)