

KEMET Part Number: C2220C105KARACTU
(C2220C105KARAC7800)

Ceramic, TipAndRing-(CxxxxC), 1 uF, 10%, 250 V, 2220, X7R, SMD, MLCC, Tip & Ring, Temperature Stable



Dimensions

L	5.7mm +/-0.4mm
W	5mm +/-0.4mm
T	1.5mm +/-0.15mm
B	0.6mm +/-0.35mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	1000

General Information

Style:	SMD Chip
Series:	TipAndRing-(CxxxxC)
Chip Size:	2220
Description:	SMD, MLCC, Tip & Ring, Temperature Stable
Features:	Temperature Stable
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	1 uF
Capacitance Tolerance:	10%
Voltage DC:	250 VDC
Dielectric Withstanding Voltage:	625 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	1 GOhms