


Film, Metallized Polypropylene, Power, C4AT, 2.2 uF, 5%, 700 V, 70C, Lead Spacing = 27.5mm



**Dimensions**

L	32mm NOM
H	33mm NOM
T	18mm NOM
S	27.5mm +/-0.4mm
LL	6mm -2mm

**Packaging Specifications**

Packaging:	Bulk
Packaging Quantity:	80

**General Information**

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	C4AT
Features:	Switching
RoHS:	Yes
Lead:	Wire Leads

**Specifications**

Capacitance:	2.2 uF
Capacitance Tolerance:	5%
Voltage DC:	700 VDC
Voltage AC:	400 VAC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Dissipation Factor:	0.05%
Max dVdt:	119 V
Resistance:	4 mOhms (100kHz)
Current:	14 Amps (100kHz 70C), 260 Amps (Peak)